

BUREAU VERITAS
Certification



OMRON DALIAN CO., LTD.

PLANT 1: NO. 3, SONG JIANG ROAD, ECONOMIC & TECHNICAL DEVELOPMENT ZONE,
DALIAN, P. R. CHINA POST CODE: 116600,

PLANT 2: NO. 28, DONG BEI ER STREET, ECONOMIC & TECHNICAL DEVELOPMENT ZONE,
DALIAN, P. R. CHINA, POST CODE: 116600

Unified social credit code: 91210213604814910L

Bureau Veritas Certification Holding SAS - UK Branch certifies that the Management System of the above organisation has been audited and found to be in accordance with the requirements of the management system standards detailed below

ISO 14001:2015

Scope of certification

DESIGN DEVELOPMENT, MANUFACTURING AND DISTRIBUTION OF ELECTRONIC SPHYGMOMANOMETERS, ELECTRONIC CLINICAL THERMOMETERS, INFRARED CLINICAL THERMOMETERS, ELECTRONIC THERAPY DEVICES (ELECTROANALGESIC TRANSCUTANEOUS STIMULATORS), TENS DEVICES, PEDOMETERS, INHALERS, NEBULIZERS, BODY FAT ANALYZERS, BODY WEIGHT & COMPOSITION MONITORS, ELECTRIC TOOTHBRUSHES, SLEEPING MONITORS, CARDIOVASCULAR PROFILING SYSTEMS AND OXYGEN GENERATORS

Original cycle start date:	3 APRIL 2001
Expiry date of previous cycle:	NA
Recertification audit date:	NA
Recertification cycle start date:	23 JUNE 2019

Subject to the continued satisfactory operation of the organisation's Management System, this certificate expires on: **22 JUNE 2022**

Certificate No.: **CNBJ313202E-UK**

Version: **No.1**, Revision date: **18 MARCH 2019**

Signed on behalf of BVCH SAS UK Branch



Certification body address: 5th Floor, 66 Prescott Street, London E1 8HG, United Kingdom

Local office address: Rm. B, F4, No.1288, Waima Road, Huangpu District, Shanghai, China. 200011

Further clarifications regarding the scope of this certificate and the applicability of the management system requirements may be obtained by consulting the organisation.

To check this certificate validity please call: (+86 10 59683663)

Certified organisation has to accept and pass regular surveillance audits, then this certificate can be continuously valid. Information of this certificate may be obtained by visiting CNCA website (www.cnca.gov.cn).